



Aperiodic port is optional

B-B (0.16 : 1)

A (0.32 : 1)

Material: 19mm MDF
 Finish: To your liking
 Damping material: Lightly stuffed and evenly distributed - approx. 50g of damping material
 Optional aperiodic port: 12g of damping material
 The damping material should be held in place with a metal grid
 Port may also be placed on the rear of the cabinet

| | | | | |
|------------------------|------------|-------------|---------|--------------------|
| Designed by haavard | Checked by | Approved by | Date | Date 28.06.2012 |
| | | | A26_cab | |
| | | | Edition | Scale |